



DIN 908
Tapón de cierre, galvanizado


Nº de pedido	Artículo nº	R	L	L1	ØD	SW (entrecaras)	Presión efectiva máx. [bar]	Peso [g]
69393	908-G1/8	G1/8	8	3	14	5	400	6
69419	908-G1/4	G1/4	12	3	18	6	400	13
176701	908-G3/8*	G3/8	12	5	24	8	400	22
179952	908-M16x1,5*	M16x1,5	12	5	22	8	400	24


Nº 908S
Tornillo de purga de aire, galvanizado


Nº de pedido	Artículo nº	R	L	L1	ØD	SW (entrecaras)	Presión efectiva máx. [bar]	Peso [g]
326389	908S-G1/8*	G1/8	8	4	14	5	400	6
343632	908S-G1/4*	G1/4	12	5	19	6	400	17


DIN 7603
Forma A anillo de obturación Cu


Nº de pedido	Artículo nº	L	ØD	ØD1	Presión efectiva máx. [bar]	Peso [g]
69815	7603-Form A-G1/8	1,0	13,5	10,0	400	0,5
69823	7603-Form A-G1/4	1,5	18,0	13,5	400	1,0


Ejemplo de montaje:

- 1) Cilindro de vástago hueco N° 6920
- 2) Anillo de obturación DIN 7603A
- 3) Boquilla roscada N° 6993
- 4) Manguera de alta presión N° 6985
- 5) Conector N° 6990-G1/4S
- 6) Manguito N° 6990-G1/4M

