

# Support element, adjustable ± 5 mm

### No. 6210S

## Support element, adjustable ± 5 mm

Housing: tempered steel, gas-nitrided and oxidised.



Order	Size	H ±0.01	Weight
			[g]
532416	K10	95-105	974
532432	K20	95-105	2020

### **Application:**

The adjustable support element allows workpieces or fixtures to be received into the bore for the pull-stud, K10 or K20 depending on the version, and clamped to the main or intermediate elements. Thanks to the adjustment and counter option, the support element can be steplessly adapted to the workpiece contour by  $\pm$  5 mm.

This clamping system can be used to move workpieces to the required machining height in the machine for 5-sided machining, or for the safe and quick clamping of workpieces with ledges and different clamping heights on the machine table.


#### Advantage:

Simple, quick and flexible clamping of complex workpiece contours on the machine table. Especially suitable for levelling workpieces or clamping fixtures at the necessary machine heights in the machine tool and for the reliable clamping of same.

#### Note:

Order numbers for the centering sleeves:

- Ø15: Order no. 535732
- Ø16: Order no. 78006
- Ø22: Order no. 78238



#### **Dimensions:**

Order no.	Size	dia. B1		dia. D1 0/+0,01		dia. D3	dia. D4	E1	G	H1	М	R	S1	SW	SW1
532416	K10	9	78	-	15	35	38	5,0	M8	98-108	M8	50	4,5	30	27
532432	K20	13	112	25	16	43	45	11,5	M12	100-110	M12	80	5,5	41	30



Subject to technical alterations.